

PRESSALIT®

GUARANTEED DURABILITY

Long-lasting quality

Pressalit Comfort D2 has a resistant design. The seat is suitable for everyday use and is made of colour ingrained duroplast, so scratches won't show. You get 10 year's warranty.

DESIGN Stylish and minimal

Solid design, high functionality and durability, inside out.



A PIECE OF DANISH DESIGN HISTORY

Pressalit Comfort D2 was designed in-house at Pressalit. The seat has a harmonic overall design that is pure in form. The composed wrap-over seat combines streamlined simplicity with a fully harmonious shape, which makes it blend with the porcelain. Timeless, delicate appearance with high functionality and durability. The seat

is very comfortable, even when the lid is down. Maximum load is $240 \mathrm{kg}$.

The first Comfort toilet seat – A classic design icon that was designed by Sigvard Bernadotte og Acton Bjørn in 1966. A proud design tradition was born.

PRESSALIT®

European Sales Agencies

Leith House, 39 Campion Drive Tanfield Lea, Stanley Co Durham, DH9 9PQ, United Kingdom T: +44 1207 236622 F: +44 1207 236633

F: +44 1207 236633 info@europeansalesagencies.com www.europeansalesagencies.com

Pressalit A/S

Pressalitvej 1 8680 Ry, Denmark T: +45 8788 8788 F: +45 8788 8789 pressalit@pressalit.com www.pressalit.com





Fits the following toilets



Laufen Pro

Duravit Me By Starck





Villeroy & Boch Architectura

Villeroy & Boch O.Novo

Premium Bathroom Solutions since 1954

Pressalit A/S is a Danish privately owned company with production facilities in Ry, Denmark. Since 1954, we have been designing and producing toilet seats of the highest quality. And since 1975, Pressalit has also been developing accessible bathrooms and height-adjustable kitchens for people with reduced mobility. This has made us one of the world's leading manufacturers of premium bathroom solutions. High quality, flawless design and reliable functionality are the core features of our wide range of products.

Bacteria-resistent Polygiene

Certificeret Polygiene® effect, which prevents the growth of bacteria 24 hours a day.



Pressalit Comfort D2

1050011-DK3999 with soft close and lift-off, white polygiene



1050111-DK3999 with soft close and lift-off, black polygiene




1084011-DK4999 with soft close and locking mechanism, white polygiene



1084111-DK4999 with soft close and locking mechanism, black polygiene





PRESSALIT SUPPORTS UNITED NATIONS GLOBAL AND UNICEF













