

PRESSALIT®

FURTHER THAN **THE FUTURE**

**SOLID** PRO

# FURTHER THAN

## 02

The aluminium pipe's silk-matte surface is resistant to chemical and mechanical stress.

## 01

The Solid Pro system can be mounted on a wide range of toilet bowls, thanks to the reversible fittings and adjustable discs.



# SOLID PRO

Pressalit introduces the market's first institutional fittings with soft closing. The Solid Pro fittings improve stability, while increasing both comfort and aesthetics. With the matching Projecta Solid Pro toilet seat, the fittings represent an aesthetic whole with dynamic curves and surprising refinements.

The Projecta Solid Pro has been thoroughly strength-tested - both in Pressalit's own test laboratory and through field tests, where intense loads and heavy-handed treatment are part of everyday use. Seat and fittings are supplied assembled for direct mounting onto a wide range of toilet bowls.

# THE FUTURE

## 03

The Solid Pro fittings allow you to mount the seat without the lid. Available with as well as without soft closing function.

## 04

The toilet seat comes ready assembled with the Solid Pro fittings for direct mounting onto the toilet bowl. It cannot be taken apart by the end-user, thus reducing the risk of theft.

## 05

The fittings are solid-cast, which means no holes or slits for dirt to gather. The fittings are also easy to clean underneath.


## 06

The Projecta Solid Pro has been tested according to DIN 19516, which among other things, is a test for the soft closing system as well as for the load capacity of the seat. The soft closing system must be able to withstand 30,000 drops (where the toilet seat closes by itself) and 13,000 forced drops (where it is forced to close). The lid and ring seat are tested with a maximum load of 240 kg.

## 07

Tests have proven just how strong the system is: in a sideways transfer test, the toilet seat was subjected to 60,000 loads of 20 kg. This equates to 16 times of usage daily over 10 years.


**PATENT  
PENDING**



# FEATURING SOFT CLOSING

## SOFT CLOSING

We already know this feature from private homes, but now this quiet luxury is available for the project market as well. Solid Pro is the market's first institutional fittings with soft closing. It increases both the comfort and lifetime of the toilet seat, as the solution puts an end to hard slams. With the soft closing function, the seat and lid drop gently and calmly onto the bowl.



# SEATS FOR

## MINIMALIST DESIGN

The Projecta Solid Pro has a slim profile and a harmonious, curved look. The back edge reveals a sophisticated peek of the silk-matte aluminium pipe, which is part of the Solid Pro hinge. The toilet seat is available in black and white with Polygiene, which prevents bacterial growth. It comes in both a Uni- and a D-shape, and with or without a lid.

# PROJECTA SOLID PRO

## THE PROJECTA SOLID PRO WITH SOFT CLOSING

The Projecta Solid Pro with the Solid Pro institutional hinge means improved strength and stability in a unique combination with the soft closing function.

## THE PROJECTA SOLID PRO WITHOUT SOFT CLOSING

The Projecta Solid Pro is also available without the soft closing function, but with the same stable Solid Pro hinge. This enables the project market to select improved strength and stability - even on small budgets.



# THE FUTURE



## **THE OBJECTA PRO WITH UNIVERSAL FITTINGS**

The Objecta Pro with antibacterial Polygiene is particularly well-suited to the project market. With its slim design and universal hinges, this seat fits a wide range of toilet bowls.

## **THE OBJECTA PRO WITH FIXED FITTINGS**

The Objecta Pro with fixed fittings, perfectly fits a wide range of toilet bowls. A harmonious design with high breaking strength and Polygiene effect makes the Objecta Pro a safe choice.

# OBJECTA PRO

## **SLIM DESIGN**

The Objecta Pro has the same design as the Projecta Solid Pro, but the mounting is different, using fixed or universal hinges. But with the same materials, the same colours and the same high breaking strength. With the Projecta Solid Pro and the Objecta Pro, the project market gains more options for choosing a strong design.




## Pressalit Projecta Solid Pro

### WITH SOFT CLOSING


No. 1004 with cover / no. 1003 without cover  
Incl. DG4 combi hinge, universal, top + bottom mounted. 011 White Polygiene, 111 Black Polygiene

### STANDARD

No. 1002 with cover / no. 1001 without cover  
Incl. DG4 combi hinge, universal, top + bottom mounted. 011 White Polygiene



DG4



### SUITABILITY LIST

Duravit Duraplus Colomba, Jika Zeta, Laufen Jika Dino, Sphinx Econ II, V&B Grangracia, V&B Saval, Wisa BW Sydney, Id. Stand. Eurovit.




## Pressalit Projecta D Solid Pro

### WITH SOFT CLOSING

No. 1008 with cover / no. 1007 without cover  
Incl. DG4 combi hinge, universal, top + bottom mounted. 011 White Polygiene, 111 Black Polygiene

### STANDARD

No. 1006 with cover / no. 1005 without cover  
Incl. DG4 combi hinge, universal, top + bottom mounted. 011 White Polygiene



DG4



### SUITABILITY LIST

Keramag Ren. No 1, Keramag iCon, Laufen Pro, V&B O. novo, Vitra S50, Vitra S50 Clean, Sphinx 345, Sphinx 345 Compact.




## Pressalit Objecta Pro


### STANDARD

No. 990 with cover / no. 989 without cover  
Incl. DF7 fixed hinge, bottom mounted / DH4 combi hinge, univertical, top + bottom mounted\*. 011 White Polygiene, 111 Black Polygiene


\* Only in colour 011 White Polygiene



DF7



DH4



### SUITABILITY LIST

Duravit Duraplus Colomba, Jika Zeta, Laufen Jika Dino, Sphinx Econ II, V&B Grangracia, V&B Saval, Wisa BW Sydney, Id. Stand. Eurovit.




## Pressalit Objecta D Pro


### STANDARD

No. 998 with cover / no. 997 without cover\*  
Incl. DF7 fixed hinge, bottom mounted / DH4 combi hinge, univertical, top + bottom mounted. 011 White Polygiene, 111 Black Polygiene

\* Only in colour 011 White Polygiene



DF7



DH4



### SUITABILITY LIST

Keramag Ren. No 1, Keramag iCon, Laufen Pro, V&B O. novo, Vitra S50, Vitra S50 Clean, Sphinx 345, Sphinx 345 Compact.



### Pressalit A/S

Pressalitvej 1  
8680 Ry, Denmark  
T: +45 8788 8788  
F: +45 8788 8789  
pressalit@pressalit.com  
www.pressalit.com

### European Sales Agencies

Leith House, 39 Campion Drive Tanfield Lea, Stanley  
Co Durham, DH9 9PQ, United Kingdom  
T: +44 1207 236622  
F: +44 1207 236633  
info@europeansalesagencies.com  
www.europeansalesagencies.com  
www.pressalit.com