

LET'S MAKE
ROOM FOR
DESIGN

PRESSALIT®




Toilet Seats

With a 67 year long reputation for making toilets seats with a positive design difference, you can't afford to ignore what will always be appreciated. We ensure that the one stand out feature people will use in the bathroom, is what we invite them to sit on, and that is – **the best seat in the house.**

Pressalit has a wide range of designs to suit most toilets used in the Australian market, so if you have a desire to seek a better outcome in your bathrooms, we can help.



MADE IN DENMARK



LIFT-OFF
 Easy cleaning. With a simple movement, the seat is removed from the toilet for thorough cleaning. The bathroom is always welcoming.



SOFT CLOSE
 Feather-light luxury. A gentle nudge is all it takes to close the seat in a smooth movement.

Create luxury in everyday life

Slim profile and featherlight lines are why the Pressalit SWAY D2 is well-composed design at its best. High functionality and streamlined elegance, which is hand-crafted by Pressalit's in-house designer Lars Herold. The soft sweeping and delicate shape are proof of a perfect meeting between masculine stringency and feminine curves.

In 2016, our SWAY D toilet seat won the Red Dot Design Award, the biggest international recognition in the design world.


The Pressalit SWAY D2 is a must-have for the discerning minimalist

Pressalit Sway D2


- | | |
|-----------------|--------------------------|
| Anthracite Grey | Product no 994112-DF4999 |
| Black | Product no 994001-DF4999 |
| Matt Black | Product no 994231-DF4999 |
| Matt White | Product no 994230-DF4999 |
| White | Product no 994000-DF4999 |



reddot design award



PERFECT FIT
 A sure match. The seats fits many toilets.



GUARANTEED DURABILITY
 Resistant design. The seat is suitable for everyday use and is made of colour ingrained duroplast, so scratches won't show. You get 10 years warranty.



Pressalit 2000

Our best-selling toilet seat, that's been used in the Australian commercial market for over 30years. The lid on the Pressalit 2000 is smaller than the seat ring itself, giving it a light and elegant design.



Pressalit 2000 with lid

White	Product no 124000-UN3999
Black	Product no 124001-UN3999
Manhattan	Product no 124052-UN3999

Pressalit 2000 without lid

White	Product no 49000-UN3999
-------	-------------------------

Pressalit Objecta D

This is a simple and practical toilet seat, specially developed those toilets which receive high traffic usage and demand large capacity load qualities. Lars Herold.

Pressalit Objecta D with lid

White	Product no 172011-D28999
Black	Product no 172111-D28999

Pressalit Objecta D without lid

White	Product no 171011-D28999
Black	Product no 171111-D28999




Polygiene®
SAFER TO TOUCH



Pressalit Dania

Where compliance to AS1428.1 - 2021 is required, the Dania toilet seat offers the appropriate design and colour attributes this Australian Standard demands.



Pressalit Dania with lid

Grey	Product no R37112-D92999
------	--------------------------

Pressalit Dania without lid

Grey	Product no R27112-D92999
------	--------------------------



Pressalit wall bin

You use your wall bin for waste, but what if waste could also be used to produce your wall bin? At Pressalit, we asked ourselves the same question. This is why the inner bucket in our new wall bin is made from recycled plastic waste.

This means that you can furnish your bathroom in a stylish way and with a good conscience. The plastic in the inner bucket is produced from recyclable materials, which can be recycled again, once the bucket is no longer needed.

Stylish and minimalistic

The wall bin has a minimalistic and clean design. It is perfectly suited for modern bathrooms and the design expression harmonises well with the designs found in our range of exclusive toilet seats and beautiful accessories. The inner bucket is grey and contrasts well with the white exterior.

The wall bin is easily opened with a fingertip in a soft and silent motion. And the wall bin remains open, even when you let go of it. So there is no need to worry about the lid closing before you have finished using it.



Easy to clean, with or without a bin liner

You can easily use the wall bin with a bag or choose to rinse out the removable inner bucket if you prefer not to use a bin liner. The inner bucket is designed with rounded corners for effective cleaning.

The wall bin also allows for easier floor cleaning. The wall bin takes up almost no space in the room and you do not need to move it when cleaning the floor.

Pressalit Wall Bin

Colour, white, Product no 1090000

Pressalit Pty Ltd (Australia)
tkn@pressalit.com
T: 0415 425 461

Pressalit.com

PREMIUM BATHROOM SOLUTIONS SINCE 1954

Pressalit A/S is a Danish privately owned company with production facilities in Ry, Denmark. Since 1954, we have been designing and producing toilet seats of the highest quality. And since 1975, Pressalit has also been developing accessible bathrooms and height adjustable kitchen solutions for people with reduced mobility. This has made us one of the world's leading manufacturers of premium bathroom solutions. High quality, flawless design and reliable functionality are the core features of our wide range of products.

PRESSALIT SUPPORTS UNITED NATIONS GLOBAL GOALS



Pressalit's Environmental and Quality Management Systems are certified by LRQA