

LET'S MAKE  
ROOM FOR  
DESIGN

## Pressalit **STYLE**

Let elegance and your personal style shine through with Pressalit Style. With the long, elegant and graphic silhouettes, you can make a standout design for your bathroom, which not only makes it more aesthetically pleasing, but also shows that you have made a conscious choice to include extraordinary design in your home.

NEW

PRESSALIT<sup>®</sup>



LET'S MAKE  
ROOM FOR  
DESIGN

### Anything but standard

Imagine a bathroom where you get to show exclusive and beautiful design that is just edgy enough to stand out.

Pressalit Style has been developed by Pressalit in-house and much thought has gone into the final design.

*"The Pressalit Style design is anything but standard. Extravagance and exclusivity is achieved in an abundance of material with which we combine contrasts and create depth, all the while aiming for a graphic lightness through the use of straight lines and geometrical shapes. As simple as that."*


### Visible minimalism

Beauty emerges through repetition and simplicity. That is clear when you chose an accessory range like Pressalit Style. It brings you the joy of extraordinary design that only becomes more beautiful and obvious when used in the whole bathroom.

### Accessories for the entire home


And why stop here? When you also implement the style with hooks in the kitchen, hallway or perhaps in the bedroom, it is easy to create greater sense of coherence throughout your home. And your decor will exude calm and a sense of exclusivity.

# Pressalit STYLE



**Towel hook, 2 pcs.**

Brushed steel	PR10100
Chrome	PR20100
Matt black	PR40100
Brushed brass	PR70100




**Towel hook, large, 2 pcs.**

Brushed steel	PR10150
Chrome	PR20150
Matt black	PR40150
Brushed brass	PR70150




**Toilet paper holder**

Brushed steel	PR10200
Chrome	PR20200
Matt black	PR40200
Brushed brass	PR70200



**Toilet paper holder w/cover**

Brushed steel	PR10220
Chrome	PR20220
Matt black	PR40220
Brushed brass	PR70220




**Wiper**


Brushed steel	PR10600
Chrome	PR20600
Matt black	PR40600
Brushed brass	PR70600

**Holder for wiper  
Blades for wiper**


PR00650
PR00600




Installation of holder on tile wall



Installation of holder on shower screen



Mounting holder on shelf



**Spare paper holder**

Brushed steel	PR10260
Chrome	PR20260
Matt black	PR40260
Brushed brass	PR70260




Brushed steel    Chrome    Matt black    Brushed brass

**Material description:**


Products: Zamak (zinc) and AISI 304 stainless steel  
 mounting brackets: Zamak (zinc)  
 Holder for wiper: ABS  
 Wiper blade: TPE  
 Zamak is a mix of zinc, aluminium, magnesium and copper.

# Pressalit **STYLE**




**Towel rail bar, single, 610 mm**

Brushed steel	PR10500
Chrome	PR20500
Matt black	PR40500
Brushed brass	PR70500




**Towel rail bar, single, 810 mm**

Brushed steel	PR10510
Chrome	PR20510
Matt black	PR40510
Brushed brass	PR70510



**Towel rail bar, double, 610 mm**

Brushed steel	PR10550
Chrome	PR20550
Matt black	PR40550
Brushed brass	PR70550





**Towel rail bar, double, 810 mm**

Brushed steel	PR10560
Chrome	PR20560
Matt black	PR40560
Brushed brass	PR70560



## EASY INSTALLATION

Choose glue or screws and get a strong result



**Shelf**


Brushed steel	PR10410
Chrome	PR20410
Matt black	PR40410
Brushed brass	PR70410



# Pressalit **STYLE**



**EASY TO FIT**  
Select the glue or screws  
and get a strong result




- Toilet brush**
- |                     |         |
|---------------------|---------|
| Brushed brass/white | PR70810 |
| Brushed brass/black | PR70800 |
| Brushed steel/white | PR10810 |
| Brushed steel/black | PR10800 |
| Chrome/white        | PR20810 |
| Chrome/black        | PR20800 |
| Matt black          | PR40800 |




- Soap dispenser**
- |                     |         |
|---------------------|---------|
| Brushed brass/white | PR70710 |
| Brushed brass/black | PR70700 |
| Brushed steel/white | PR10710 |
| Brushed steel/black | PR10700 |
| Chrome/white        | PR20710 |
| Chrome/black        | PR20700 |
| Matt black          | PR40700 |

## GLUE YOUR ACCESSORIES ON and experience the advantages

- The wet room membrane remains intact
- Tiles don't break
- Load-bearing capacity of up to 200 kg




## EASY TO FIT with glue on untreated surfaces



Tiles



Concrete




Tiles




Metal



Glass



Wood



- Toilet bin**
- |                     |         |
|---------------------|---------|
| Brushed brass/white | PR70960 |
| Brushed brass/black | PR70950 |
| Brushed steel/white | PR10960 |
| Brushed steel/black | PR10950 |
| Chrome/white        | PR20960 |
| Chrome/black        | PR20950 |
| Matt black          | PR40950 |




Scan the QR code  
and see how.  
Glue not included.

Glue

PR00999





Pressalit A/S  
Pressalitvej 1  
8680 Ry, Denmark  
T: +45 8788 8788  
F: +45 8788 8789  
pressalit@pressalit.com

Pressalit.com



## PREMIUM BATHROOM SOLUTIONS SINCE 1954

Pressalit A/S is a Danish privately owned company with production facilities in Ry, Denmark. Since 1954, we have been designing and producing toilet seats of the highest quality. And since 1975, Pressalit has also been developing accessible bathrooms and height adjustable kitchens for people with reduced mobility. This has made us one of the world's leading manufacturers of premium bathroom solutions. High quality, flawless design and reliable functionality are the core features of our wide range of products.

### PRESSALIT SUPPORTS UNITED NATIONS GLOBAL GOALS



Pressalit's Environmental and Quality Management Systems are certified by LRQA